



# PORTABLE SLIT LAMP Kowa SUSSE

4 colors!





# Kowa Portable Slit Lamps are Now LEDs!

Enhanced portability during examination, the SL-15L features a sculpted grip for easy handling, light-weight design, long-term illumination, and an optional camera connection adapter. SL-15L is a highly portable slit lamp perfect in any situation.

# **Features**

- 1. 20,000 lux white LED lamp source
- 2. A large-capacity battery permits long-term continuous lighting.(Approx. 480 minutes)
- 3. Cordless and rechargeable for unrestricted examination anywhere (Kowa SL-15 power source unit is also available.)
- 4. The lighting switch on the grip can be turned on with just a light press.
- 5. Easy selection between 3 slit widths and spot illumination
- 6. Quick, one-touch selection of either 10x or 16x magnification
- 7. Built-in blue filter
- 8. The stand doubles as a battery charger.
- 9. A lithium-ion rechargeable battery is utilized to make the unit compact and light.
- 10. Simultaneous charging of the main unit and spare battery
- 11. Supports electronic image with the optional camera connection adapter (C-mount)



# Optional accessories



Camera connection adapter, barrier filter and diffusion cylinder



Head rest



Spare lithium ion battery (Power pack)



Carrying trunk case

# **Specifications**

## Slit lamp (main unit)

| Microscope                      |  |  |
|---------------------------------|--|--|
| Angle of convargence            | 13°  |  |
| Total Magnification             | 10x and 16x                                |  |
| Working distance                | Approx. 80 mm (at 16x magnification)       |  |
|                                 | Approx. 100 mm (at 10x magnification)      |  |
| Actual field of view            | $\phi$ 10 mm (at 16x magnification)        |  |
|                                 | $\phi$ 15 mm (at 10x magnification)        |  |
| Interpupillary adjustment range | 50 to 72 mm                                |  |
| Diopter adjustment range        | -8 to +5D                                  |  |
| Slit Projector                  |  |  |
| Light source                    | White LED                                  |  |
| Slit width                      | 0.1 mm, 0.2 mm, 0.8 mm                     |  |
| Spot diameter                   | φ12 mm                                     |  |
| Light intensity adjustment      | Full, 1/4, 1/16 (3 stages, max 20,000 lux) |  |
| Slit's illuminating angle       | Horizontal, ±60°                           |  |

| Filter                         | Built-in blue filter                                |  |
|--------------------------------|---|--|
| Continuous lamp operating time | Approx. 480 minutes                                 |  |
| Electrical rating              |   |  |
| Power                          | Input: DC7.4 V                                      |  |
|                                | Power supply  |  |
| Dimensions and Weight          |   |  |
| Dimensions                     | 220(W)x95(D)x215(H) mm                              |  |
| Weight                         | 790 g (including a power pack)                      |  |
| Power source (charger)         |   |  |
| Electrical rating              |   |  |
| Output terminal                | For charging a built-in power pack and a single one |  |
|                                |   |  |

| Electrical rating     |   |  |
|-----------------------|---|--|
| Output terminal       | For charging a built-in power pack and a single one |  |
| Power supply          | Input : AC230 V 50/60 Hz                            |  |
|                       | Power Consumption : 90 VA                           |  |
| Dimensions and Weight |   |  |
| Dimensions            | 125(W)×255(D)×70(H) mm                              |  |
| Weight                | 1250 g  |  |

Specifications and appearances are subject to change without notice.

Distribution name : KOWA SL-15L





# Kowa Company, Ltd.

World Sales Headquarters

4-14, Nihonbashi-honcho 3-chome, Chuo-ku, Tokyo 103-8433, Japan

Phone: +81(3)3279-7639 Facsimile: +81(3)3279-7541 URL: http://www.kowa.co.jp/e-life/

Kowa Company, Ltd. Hamamatsu Factory

3-1, Shinmiyakoda 1-chome, Kita-ku, Hamamatsu City, Shizuoka Pref., 431-2103, Japan

#### EC REP Kowa Optimed Europe Ltd.

Sandhurst House, 297 Yorktown Road, Sandhurst, Berkshire GU47 0QA, U.K. Phone: +44(127)693-7021 Facsimile: +44(127)693-7023 URL: http://www.kowamedical.com/

## Kowa Optimed Deutschland GmbH

Bendemannstrasse 9.

40210 Duesseldorf, F.R. Germany

Phone: +49(211)54218400 Facsimile: +49(211)54218410 URL: http://www.kowamedical.com/

> REF SL151\_1491300C0 Printed in Japan.

